CLOSED CIRCUIT COOLER MODEL# ESW4 9-42I9-LP NTS


EVAPCO, INC. Evapeo




WX409094804P-DRA-ST SERIAL# 10/26/2025


NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS COIL SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- 6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 7. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN**
- [METRIC] [mm] 8. * - APPROXIMATE DIMENSIONS DO NOT USE





FACE A



FACE A

NO. OF SHIPPING SECTIONS DRAWN BY: OPERATING SHIPPING 9250 lbs+ [4200] kg+ 13010 lbs+ [5905] kg+ HEAVIEST SECTION 5880 lbs+ [2665] kg+ **AWT** WEIGHT WEIGHT WEIGHT