CLOSED CIRCUIT COOLER


MODEL # ESW4 9-45J6-LP SCALE NTS

EVAPCO, INC. EVEPCO


DWG.# WX409064810P-DRA-ST REV SERIAL# DATE: 11/25/2025

NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS COIL SECTION
- 3. MPT DENOTES MALE PIPE THREAD
 FPT DENOTES FEMALE PIPE THREAD
 BFW DENOTES BEVELED FOR WELDING
 GVD DENOTES GROOVED
 FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- 6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]
- 8. * APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING



FACE C



FACE A



FACE A

 SHIPPING WEIGHT
 8740 lbs+ [3965] kg+
 OPERATING WEIGHT
 12020 lbs+ [5455] kg+
 HEAVIEST SECTION WEIGHT
 6180 lbs+ [2805] kg+
 NO. OF SHIPPING SECTIONS
 2
 DRAWN BY: WEIGHT
 AWT