

UNIT	CLOSED CIRCUIT COOLER
MODEL #	ESW4 9-45J18-SP

EVAPCO, INC.



DWG. # WX409184810P-DRA-ST

REV -

SCALE	NTS
-------	-----


SERIAL #

DATE: 1/20/2026

NOTES:

- (M) FAN MOTOR LOCATION
- HEAVIEST SECTION IS COIL SECTION
- MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]


- * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- COIL CONNECTIONS LOCATED ON FACES B AND D



FACE B

(2) 4" [100] BFW
FLUID IN


FACE B
PLAN VIEW



FACE B & D
COIL CONNECTIONS


(2) 1/2" [15] FPT
VENT

FACE C



FACE D

FACE A



FACE A

SHIPPING
WEIGHT

22580 lbs+ [10245] kg+

OPERATING
WEIGHT

31820 lbs+ [14435] kg+

HEAVIEST SECTION
WEIGHT

15220 lbs+ [6905] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY: AWT