COOLING TOWER	EVADCO	TNIC evapco	DWG. # CT4C072848-DRA-ST	REV -
MODEL# AT 27-4H28 SCALE NTS	EVAPCO,	INC. Evapeo	SERIAL#	DATE: 11/21/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS FAN/CASING SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 7. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]	FACE	(M) ACCESS DOOR VIEW		FACE D
1'-9 3/8" [543]	2'-11 3	3/8" [898] ACCESS DOOR DOOR	(M)	SSS
(2) 8" [200]	- (2) 2" [50] MPT	/8" [1959]		
BFW/GVD INLET		/4" [1683]		
(2) 3" [80] MPT OVERFLOW (2) 8" [200]	4 1/4"	3/8" [35]	2 1/2" [64]	

(2) 8" [200] BFW/GVD OUTLET

7'-4" [2235] **FACE B** 1'-9 1/4" [540] 3'-1 3/4" [959]

28'-2" [8585]

FACE A