| CLOSED CIRCUIT COOLER | | | EVAPCO | TNC | evapco | DWG.# WX409184806P-DRA- | | |
|---|--|--|-----------------------------|--|-----------------------|----------------------------|-------------------------|--|
| MODEL# | ESW4 9-43K18-LP | SCALE NTS | LVAICO | | | SERIAL# | DATE: 10/15/2025 | |
| 2. HEAV 3. MPT I FPT I BFW GVD FLG I 4. +UNI ACCE 5. 3/4" [REFE SUPF 6. MAKE 20 ps | AN MOTOR LOCATION PIEST SECTION IS COIL SECTION IN THE COIL SECTIO | AD READ /ELDING JDE RY DRAWINGS) ES. EL 344 kPa] | (2) 4" [100] BFW | FACE B PLAN VIEW (2) 4" [100] BFW FLUID OUT | (M) | (M) | FACE D | |
| EN [M 8. * - AP FOR I | INSIONS LISTED AS FOLLOW IGLISH FT-IN ETRIC] [mm] PROXIMATE DIMENSIONS I PRE-FABRICATION OF CON CONNECTIONS LOCATED C | DO NOT USE NECTING PIPIN | | * 1'-7 1/2" [495] * 2'-2 3/8" [670] | <u>FAC</u> | <u>CE A</u> | ⊢1'-0 7/8" [327] | |
| | Ţ | | * 2'-8" [813] | _* 2'-10 3/4" [883] | | | 1 1 1 1 1 1 | |
| | (M) | | FACE B & D COIL CONNECTI | | [M) ACCESS DOOR DOOR | C(M) ACCESS DOOR | 9'-3 1/4" [2826] | |
| | | | | | 6 | | 18'-1 7/8" [5536] | |
| | 2" [50] MPT — MAKE-UP 2" [50] MPT — DRAIN | | 3" [80] MPT OVERFLOW | (2)1/2" [15] FPT | | | 8'-10 5/8" [2709] | |
| | 2'-3" [686] | | | | | | | |
| | 3 3/8" [86] 4 1/4" [107] 5 1/4" [132] | - | 2'-5 5/8" [752] | 2'-2 1/4" [667] | 18 ² | 86] | | |
| | [102] | 8'-5 1/2" [2578] FACE B | | FACE A | | | | |
| SHIPPING WEIGHT | 19380 lbs+ [8795] k | | 27420 lbs+ [12440] kg+ | HEAVIEST SECTION WEIGHT | 11830 lbs+ [5365] kg+ | NO. OF SHIPPING SECTIONS 2 | DRAWN BY: AWT | |