COOLING TOWER			EVAPCO, INC. EVEPEO SER				NG. # T4142436-DRA-	-ST	EV
ODEL #	AT 114-3P24	SCALE NTS	EVAPO	O, IN		SEI	RIAL #	D	ATE11/11/2025
2. HEAVIES 3. MPT DEI FPT DEN BFW DE GVD DEI FLG DEN PE DEN 4. +UNIT W 20 psi MI 6. 3/4" [19N REFER T DRAWIN 7. DIMENS ENG	I MOTOR LOCATION BY SECTION IS UPPER SI NOTES MALE PIPE THRE NOTES FEMALE PIPE THE NOTES BEVELED FOR W NOTES GROOVED NOTES FLANGE DIES PLAIN END JEIGHT DOES NOT INCLU- ORIES (SEE ACCESSOR P WATER PRESSURE N [137 kPa], 50 psi MAX [3 M] DIA. MOUNTING HOLI TO RECOMMENDED STEI G IONS LISTED AS FOLLOV LISH FT-IN RIC] [mm]	AD READ /ELDING JDE Y DRAWINGS) 344 kPa] ES. EL SUPPORT		PLA	FACE B	FAC	ACCESS DOOR	FACE D	
			7" [178]	1'-!	5 1/4" 438]				
		1	10'-2 1/4" [3105]	_			<u> </u>		
			2" 51] 18'-5 1/2" [5626]			11'-10 1/2"	14" [350] BFW/GVD INLET		
			8'-3 1/4" [2521]	12'-3 3/4"	+				
				2'-2" [660] 1'-5 3/8"	9" [229] -	4" [100] FPT	14" [350] BFW/GVD OUTLET		
	13'-11 1/4" [4248] FACE B	'	3/8" [9]	9" [229] 4 1/8" [105]		11'-10 1/2" [3620] 23'- [72:	-9" 39]		
	<u></u>					<u>FAC</u>	<u>E A</u>		
SHIPPING WEIGHT	18650 lbs+ [84	460] kg+	OPERATING WEIGHT 34500 lbs+ [1565	0] kg+	IEST SECTION WEIGHT	12380 lbs+ [5620] kg+	NO. OF SHIPPING SECTIONS	2 DRAW	^{/N BY:} MER