UNIT CLOSED CIRCUIT COOLER	EVADCO	TNIC CEVOLS) CO	wg. # WX409184810P-DRA-S	Γ REV -
MODEL# ESW4 9-45K18-SP SCALE N	TS EVAPCO	, INC. Evan	S	ERIAL#	DATE: 12/14/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWI 5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 7. DIMENSIONS LISTED AS FOLLOWS:	NGS) (2) 4" [100] BFW FLUID IN	FACE B PLAN VIEW (2) 4" [100] BFW FLUID OUT -* 2'-10 1/2" [876]	FACE	(M)	FACE D
ENGLISH FT-IN [METRIC] [mm] 8. * - APPROXIMATE DIMENSIONS DO NOT UTTO FOR PRE-FABRICATION OF CONNECTING	SE	2-10 1/2 [8/0]	<u>FACE</u>	<u> </u>	
9. COIL CONNECTIONS LOCATED ON FACES		+ 01 0 0 10 10 TO TO			_1'-0 7/8" [327 <u>]</u>
	* 2'-8"	* 2'-2 3/8" [670] * 2'-10 3/4"			
(M)	[813] FACE B & C COIL CONNECT		(M) (ACCESS)	ACCESS (DOOR)	
					9'-3 1/4" [2826]
2" [50] MPT — MAKE-UP	3" [80] MPT OVERFLOW	(2)1/2" [15] FPT VENT			19'-4 7/8" [5917] 10'-1 5/8" [3090]
2" [50] MPT — DRAIN 2'-3" [686]	OVERFLOW		0 0 0		
3 3/8" [86]	1'-6 3/8" [465]				<u>, </u>
4 1/4" [107]	2'-5 5/8"	2'-2 1/4"	18'-0		
5 1/4"	[752]	[667]	[5486 FACE		
[25	78]		<u> </u>		
FAC		UEAN/EQT GEOTION 15330	O lhou [COOF] lie	NO. OF SHIPPING SECTIONS	DRAWN BY:
SHIPPING WEIGHT 22780 lbs+ [10335] kg+	OPERATING 32020 lbs+ [14525] kg+	HEAVIEST SECTION 15220 WEIGHT) lbs+ [6905] kg+	NO. OF SHIPPING SECTIONS 2	DRAWN BY: AWT