UNIT	COOLING TOWER		EVADOO	TNIC EVODEO	DWG. # T3092848-DRD-ST	REV.
MODEL #	AT 29-4M28	SCALE NTS	EVAPCO,	INC. evapeo	SERIAL #	DATE _{12/15/2025}
2. HEAVIES 3. MPT DE FPT DEN BFW DE GVD DE FLG DEI 4. +UNIT W ACCESS 5. MAKE-U 20 psi M 6. 3/4" [19M 7. DIMENS EN	I MOTOR LOCATION ST SECTION IS UPPER S NOTES MALE PIPE THRE NOTES FEMALE PIPE TH NOTES BROOVED NOTES GROOVED NOTES FLANGE /EIGHT DOES NOT INCLE SORIES (SEE ACCESSOR P WATER PRESSURE IN [137 kPa], 50 psi MAX [MM] DIA. MOUNTING HOI ENDED STEEL SUPPOR IONS LISTED AS FOLLO GLISH FT-IN ETRIC] [mm]	EAD READ VELDING JDE RY DRAWINGS) 344 kPa] LES. REFER TO T DRAWING.	FACE B PLAN VIEW	ACCESS DOOR FACE	C (M) ACCESS DOOR	FACE D
				FACE A	<u>A</u>	
1'-9 3/8 [543]	" -	1'-7/8 [327	<u>"</u>			
	M	[2"]				
		9'-1	/2" 	6'-11 7/8"	(2) 8" [200] BFW/GVD INLET	
			10'-9 1/2" [3289]			
		5'-6 [16	1/4"			

HEAVIEST SECTION WEIGHT

-(2) 8" [200] BFW/GVD OUTLET

NO. OF SHIPPING SECTIONS

DRAWN BY: JLG


-(2) 3" [80] FPT OVERFLOW

-(2) 3" [80] FPT DRAIN

-(2) 2" [50] MPT MAKE-UP

2 1/2" [64]

4730 lbs+ [2150] kg+



22760 lbs+ [10325] kg+

OPERATING WEIGHT

13740 lbs+ [6235] kg+

SHIPPING

WEIGHT