COOLING TOWER COOLING TOWER AT 214-3N48 SCALE NTS EVAPCO, INC. SERIAL # T4144836-DRA-ST SERIAL # T4144836-DRA-ST SERIAL # T4144836-DRA-ST SERIAL # T4144836-DRA-ST SERIAL # TA144836-DRA-ST SERIAL	FACE D
1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS UPPER SECTION 3. MPT DENOTES MALE PIPE THREAD BFV DENOTES FEMALE PIPE THREAD BFV DENOTES FEMALE PIPE THREAD BFV DENOTES GROOVED FLO DENOTES GROOVED FLO DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 KPa], 50 psi MAX [344 KPa] 6. 3/4" [19MM] DIA. MOLINTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] FACE A FACE A	FACE D
10'-2 1/4" [3105] 1'-5 1/4" [438]	
10'-2 1/4" (3105) (M)	
	ı
[51] 18'-5 1/2" [3620'] INLET	ı
8'-3 1/4" [2521] 8'-2 1/4" [2521]	
2'-2"	
FACE B	
SHIPPING 35040 lbc+ [16305] kg+ OPERATING 67640 lbc+ [30685] kg+ HEAVIEST SECTION 11860 lbc+ [5380] kg+ NO. OF SHIPPING SECTIONS 1	BY: MER