

UNIT	CLOSED CIRCUIT COOLER
MODEL #	ESW4 9-42J18-SP

**EVAPCO, INC.**




DWG. # WX409184804P-DRA-ST


REV -  
SERIAL #  
DATE: 2/9/2026

NOTES:


1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS COIL SECTION
3. MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
6. MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
7. DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
[METRIC] [mm]
8. \* - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
9. COIL CONNECTIONS LOCATED ON FACES B AND D



**FACE B**



**FACE B & D  
COIL CONNECTIONS**



**FACE A**

SHIPPING  
WEIGHT

17220 lbs+ [7815] kg+

OPERATING  
WEIGHT

24660 lbs+ [11190] kg+

HEAVIEST SECTION  
WEIGHT

9860 lbs+ [4475] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY: AWT