JNIT	COOLING TOWER		EVADOO IN	DWG. # T4284848-DRA-ST	REV	
MODEL #	AT 428-4R48	SCALE NTS	EVAPCO, IN		SERIAL #	DATE _{12/15/2025}
2. HÉAV 3. MPT I FPT D BFW I GVD I FLG D PE DE 4. +UNIT ACCE 5. MAKE 20 psi 6. 3/4" [1 RECO 7. DIMEN [8. PAN F EVAPP BY OT 9. PAN E	AN MOTOR LOCATION IEST SECTION IS UPPER SE DENOTES MALE PIPE THREA DENOTES FEMALE PIPE THREA DENOTES BEVELED FOR WID DENOTES GROOVED DENOTES FLANGE ENOTES PLAIN END WEIGHT DOES NOT INCLUIT SSORIES (SEE ACCESSORY 1-UP WATER PRESSURE MIN [137 kPa], 50 psi MAX [3 9MM] DIA. MOUNTING HOLE DIMENDED STEEL SUPPORT NSIONS LISTED AS FOLLOW ENGLISH FT-IN METRIC] MM FLUME BOX EQUALIZERS SL CO. PAN EQUALIZER PIPING THERS. EQUALIZER NIPPLE IS 11'-10 EACH STEP SIDE.	AD IEAD ELDING DE / DRAWINGS) 44 kPa] ES. REFER TO DRAWING. /S: UPPLIED BY ES IS SUPPLIED	FACE E PLAN VIEW		CE C (4) ACCESS DOOR	FACE D
2" [51]	(4) 14" [350] BFW/GVD OUTLET (4) 4" [100] MPT OVERFLOW (4) 3" [80] MPT MAKE-UP (4) 4" [100] MPT DRAIN 5 1/8" [130] 28'-3 5/4 [8626		7" [178] 11'-5 1/4" [3410] 19'-5 1/2" [5931] 8'-3 1/4" [2521] 13'-3 3/4" [4058] 1'-5 3/8" [9" [229] 4" [102]	11'-10 1/2" (4) 14" [350] BPW/GVD INLET 9 1/8" [232] 1 3/8" [35] (TYP) 23'-9" [7239]	(4) 12" [300] BRW/GVD EQUALIZER (SEE NOTE #9) 1'-1" [1092]	1 1/2" [38]
FACE B						
SHIPPING WEIGHT	80560 lbs+ [3654		RATING 143960 lbs+ [65300] kg+	VIEST SECTION 14100 lbs+ [6400] kg+	NO. OF SHIPPING SECTIONS 8	RAWN BY: MER