CLOSED CIRCUIT COOLER EVAPCO, INC. Evapeo WX409124804P-DRA-ST MODEL# SERIAL# ESW4 9-42M12-SP 10/25/2025 NTS NOTES: 1. (M)- FAN MOTOR LOCATION **FACE C** 2. HÉAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD (M) FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING _ = = = **GVD DENOTES GROOVED** FLG DENOTES FLANGE 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. 3/4" [19MM] DIA. MOUNTING HOLES. **FACE B** FACE D REFER TO RECOMMENDED STEEL **PLAN VIEW** SUPPORT DRAWING 6. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 7. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] [mm] **FACE A** 8. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING _{-1'-0 7/8" [327]} ACCESS * 2'-8" (DOOR [813] 9'-3 1/4" [2826] 4" [100] BFW FLUID IN 16'-10 3/8" [5142] 4" [100] BFW FLUID OUT 2" [50] MPT MAKE-UP 3" [80] MPT 1/2" [15] FPT **OVERFLOW** VENT 2" [50] MPT DRAIN * 1'-0" [305] 7'-7 1/8" [2315] 2'-3" [686]-L* 2'-2 3/8" [670] 3 3/8" [86]-L1'-6 3/8" [465] 2'-1" 11'-11 3/4" [635] [3651] 2'-5 5/8" 4 1/4" [752] [107] * 2'-10 3/4" 5 1/4" [883] [132] 8'-5 1/2" [2578] **FACE A FACE B**

HEAVIEST SECTION

WEIGHT

7090 lbs+ [3215] kg+

OPERATING

WEIGHT

SHIPPING

WEIGHT

11350 lbs+ [5150] kg+

16500 lbs+ [7485] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY:

AWT