UNIT	COOLING TO	COOLING TOWER	
MODEL #	AT 112-2I14	SCALE NTS	

EVAPCO, INC. Evapco




DWG. # REV. T3121424-DRE-ST DATE<sub>12/14/2025</sub> SERIAL #

**SHIPPING** 

WEIGHT


- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT **DRAWING**
- 7. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] [mm]


## **FACE C**



**FACE D** 

**FACE A** 





DRAWN BY: KDS NO. OF SHIPPING SECTIONS OPERATING HEAVIEST SECTION 8230 lbs+ [3735] kg+ 5360 lbs+ [2435] kg+ 15560 lbs+ [7060] kg+ WEIGHT WEIGHT