


UNIT	COOLING TOWER	
MODEL #	AT 424-4K28	SCALE NTS

EVAPCO, INC. 



DWG. #	T3242848-DRF-ST	REV. -
SERIAL #		DATE 1/31/2026

NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
4. FPT DENOTES FEMALE PIPE THREAD
5. BFW DENOTES BEVELED FOR WELDING
6. GVD DENOTES GROOVED
7. FLG DENOTES FLANGE
8. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
9. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
10. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
11. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]



PLAN VIEW



FACE B

SHIPPING
WEIGHT

39780 lbs+ [18045] kg+

OPERATING
WEIGHT

68680 lbs+ [31155] kg+

HEAVIEST SECTION
WEIGHT

6670 lbs+ [3030] kg+

NO. OF SHIPPING SECTIONS

6

DRAWN BY: **JLG**