
UNIT	COOLING TOWER	
MODEL #	AT 217-2K12	SCALE NTS


EVAPCO, INC. Evapeo


DWG. # T3171224-DRG-ST REV. SERIAL # DATE 12/13/2025

## NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]







 
 SHIPPING WEIGHT
 10860 lbs+ [4930] kg+
 OPERATING WEIGHT
 18580 lbs+ [8430] kg+
 HEAVIEST SECTION WEIGHT
 3580 lbs+ [1625] kg+
 NO. OF SHIPPING SECTIONS WEIGHT
 4
 DRAWN BY: KDS