UNIT COOLING TOWER			DCO T	NC eve	apeo °	DWG. # T4285260-DRA-ST	REV.
10DEL # AT 428-5L52	SCALE NTS	EVA	IPCO, I	NC. EV	3	SERIAL #	DATE _{12/14/2025}
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS UPPER SE 3. MPT DENOTES MALE PIPE THREAFPT DENOTES FEMALE PIPE THREBEW DENOTES BEVELED FOR WIGOND DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCLUIT ACCESSORIES (SEE ACCESSORY 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [3] 6. 3/4" [19MM] DIA. MOUNTING HOLE REFER TO RECOMMENDED STEED DRAWING 7. DIMENSIONS LISTED AS FOLLOW ENGLISH FT-IN [METRIC] [mm] 8. PAN FLUME BOX EQUALIZERS SUEVAPCO. PAN EQUALIZER PIPING BY OTHERS. 9. PAN EQUALIZER NIPPLE IS 11'-10 OFF EACH STEP SIDE.	DE ORAWINGS) 44 kPa] SS. L SUPPORT SS: JPPLIED BY S IS SUPPLIED		FACE B		(8) ACCESS DOOR		FACE D
		1'-3 1/4" [387]	7" [178]		FACE A	<u>.</u>	
(4) 14" [350] BFW/GVD INLET		6'-11 5/8" [2124] 22'-3 1/2 [6794]	12'-1/4" [3664] [51]	00	00	00 00	2" [51]
		16'-3 3/4" [4972]	10'-3 1/4" [3131]				
(4) 3" [80] MPT // MAKE-UP 13	11'-6" 3505] '-1 1/4" 3994] '-5 1/2" 4102]	2'-2" [660] _ 1'-5 3/8" [441] _ 9" [229]			9 1/8" [232] 1 3/8" [35]	(4) 12" [300] BFW/GVD EQUALIZER (SEE NOTE #9) 3'-7" [1092]	
	11 1/4" 1248]	- [4" [102]	4.4.00	. 7043			4.4/0"
28'-3 5/8" [8626] FACE B		1 1/2"					
SHIPPING 97440 lbs+ [44200] kg+ WEIGHT		OPERATING 164760 WEIGHT	lbs+ [74735] kg+	HEAVIEST SECTION WEIGHT	17720 lbs+ [8040] kg+	NO. OF SHIPPING SECTIONS 8	DRAWN BY: MER