UNIT	COOLING TOWER	
MODEL #	AT 312-4M60	SCALE NTS

EVAPCO, INC. Evapeo

FACE B


PLAN VIEW


DWG. # T3126048-DRD-ST REV. SERIAL # DATE 12/13/2025

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]









FACE D

FACE A





FACE A

 SHIPPING WEIGHT
 40260 lbs+ [18265] kg+
 OPERATING WEIGHT
 71460 lbs+ [32415] kg+
 HEAVIEST SECTION WEIGHT
 9000 lbs+ [4085] kg+
 NO. OF SHIPPING SECTIONS WEIGHT
 6
 DRAWN BY: KDS