UNIT CONDENSER			EVAPCO, INC. Evapeo			Ī	DWG. # EG171210-DRC-ST		EV.
10DEL #	eco-ATC-649A	SCALE NTS	EVAPCO,	INC.	Evasco	9	SERIAL #	D	OATE 12/14/2025
2. HEAV 3. MPT [ FPT [ BFW   GVD I FLG [ PE DE 4. +UNIT ACCE 5. MAKE 20 psi 6. *-APP FOR F PIPIN 7. 3/4" [1 RECC 8. DIMEI	AN MOTOR LOCATION IEST SECTION IS UPPER SIDENOTES MALE PIPE THRE IENOTES FEMALE PIPE THE DENOTES BEVELED FOR WO DENOTES GROOVED DENOTES FLANGE ENOTES PLAIN END WEIGHT DOES NOT INCLU SSORIES (SEE ACCESSOR E-UP WATER PRESSURE MIN [137 kPa], 50 psi MAX [37 kPa], 50 psi MAX [47 kPa] PRE-FABRICATION OF CON G 9MM] DIA. MOUNTING HOLE MMENDED STEEL SUPPOR USIONS LISTED AS FOLLOV ENGLISH FT-IN METRIC [mm]	AD READ /ELDING  JDE Y DRAWINGS)  344 kPa] O NOT USE NECTING  ES. REFER TO RT DRAWING.			FACE B PLAN VIEW	ACCE	FACE C  (M) ACCESS DOOR  SSS DOOR (M)	FACE D	
	1' 0 2/9"		4'-3/4" * 2'-2 3/8" * [ 670 ]		1'-7/8" [ 327 ] -	<u> </u>	FACE A		
	1'-9 3/8" [ 543 ]  (4) 4" [100] PE  2'-10 1/2" * [ 876 ]  (4) 4" [100] PE  1'-11 1/8" [ 587 ]  3" [ 76 ]	2'-10 1/4" - 2'-10 1/4" - 8'-1/4" - 8'-1/4" - 8'-1 1/4" - [ 2470 ] - 8'-5 1/2" - 8'-5 1/2" - 8'-5 1/2"	REFRIG IN REFRIG OUT O  REFRIG OUT O  6" *	13'-2 3/4' [ 4032 ]					
	_		4 1/8"		1'-6 1/4" [ 464 ]		11'-11 3/4"		
			<u>CE B</u>				FACE A		

HEAVIEST SECTION WEIGHT

14370 lbs+ [6520] kg+

SHIPPING WEIGHT OPERATING WEIGHT

41080 lbs+ [18635] kg+

32480 lbs+ [14735] kg+

DRAWN BY:

NO. OF SHIPPING SECTIONS