| UNIT   |  | <u> </u>                   |  |                     | 0            | DWG.#           | REV                 |  |
|--|--|----------------------------|--|---------------------|--------------|-----------------|---------------------|--|
| CONDENSER  |  |                            | EVAPCO, INC.                             |                     | evapco       | C4122408-DRA-ST | DATE:               |  |
| MODEL #  | TC-930E                                  | NTS                        |  | <del>50, 111</del>  |              | SERIAL#         | 10/30/2025          |  |
| 00 mai MINI (407 kDa)                              |  |                            |  | FACE B<br>PLAN VIEW | ACCESS (M)   | FACE C          | ACCESS DOOR  FACE D |  |
| METRIC [mm]  |  |                            |  |                     |              | FACE A          |                     |  |
|  |  |                            | 7" [178]                                 | 1'-3 1/4" [3        |              |                 |                     |  |
|  | 5'-9 (                                   |                            | 4'-8 1/8" [1426]<br>3'-0 3/8" *<br>[922] |                     | (M) ACC DOO  |                 | ACCESS<br>DOOR      |  |
| 3'-2 3/4"[984] *                                   | (2) 4* [100] PE<br>(2) 4* [100] PE       | O REFRIG IN  REFRIG OUT  O | 5'-2" [1575]                             | 9]                  |              |                 |                     |  |
| 2" [50] MPT —<br>MAKE-UP<br>3" [80] MPT —<br>DRAIN |  |                            | 6" [152] *<br>6'-2 3/8" [1889]           |                     |              |                 |                     |  |
| 2'-1 1/4" [641]                                    | 5 1/4"<br>[133]<br>4 1/4"<br>[108]       |                            | 1'-5" [432]                              | 2'-10 3/8"_         |              | 24'-1 3/4"      |                     |  |
|  | 7'-2"<br>[2184]<br>11'-1<br>[360<br>FACE | <i>'</i> ]                 | 3" [80] MPT<br>OVERFLOW                  | [873]               | <del> </del> | [7360]  FACE A  |                     |  |

HEAVIEST SECTION WEIGHT

27520 lbs+ [12485] kg+

SHIPPING WEIGHT

34140 lbs+ [15490] kg+

OPERATING WEIGHT

46990 lbs+ [21315] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY:

JLG