UNIT CONDENSER			EV/AB/			valo e o	wg. # C4122410-DRA-ST	REV	-
MODEL #	ATC-986E	SCALE NT	EVAPO	CO, INC		S	ERIAL#	DATE:	2/15/2025
2. MPT DENO FPT DENO BFW DEN GVD DENO FLG DENO 3. +UNIT WE ACCESSO 4. MAKE-UP 20 psi MIN 5. *-APPROX FOR PRE- PIPING 6. 3/4" [19mm RECOMMI 7. DIMENSIO	MOTOR LOCATION DTES MALE PIPE THR DTES FEMALE PIPE TH OTES BEVELED FOR DIES GROOVED DTES FLANGE TES PLAIN END LIGHT DOES NOT INCL DRIES (SEE ACCESSO WATER PRESSURE [137 kPa], 50 psi MAX KIMATE DIMENSIONS I FABRICATION OF COI DIES DIES SUPPO DIS LISTED AS FOLLO ENGLISH FT-IN	HREAD WELDING LUDE RY DRAWIN [344 kPa] DO NOT USE NNECTING LES. REFER	то	FACE B PLAN VIEW		ACCESS DOOR	FACE C	CESS DOOR	FACE D
ſ	METRIC [mm]						FACE A		
			7" [178]	1'-3 1/4" [3	87]¬			_	
									_
		9 3/8 <u>"</u> * 762]	4'-8 1/8"[1426] 3'-0 3/8" * [922]			(M) ACCESS DOOR		ACCESS	
4'-0 3/4"[1238	(2) 4* [100] PE (2) 4* [100] PE	O REFRIG I REFRIG O	6'-0"[1829]	3]		9/7			
2" [50] MPT — MAKE-UP 3" [80] MPT — DRAIN 1 2'-1 1/4" [641]			6" [152] * 6'-2 3/8" [1889]						
3 5/8" [92]-	[108] [108] [2184] [11]	-10"_	3" [80] MPT OVERFLOW	2'-10 3/8''_ [873]					
FACE A									
SHIPPING WEIGHT	38480 lbs+ [17455] k	g+	OPERATING 51520 lbs+ [23370]	kg+ HEAVIEST S	ECTION HT	31860 lbs+ [14455] kg+	NO. OF SHIPPING SECTIONS 2	DRAWN BY:	JLG