UNIT CONDENSER		ΕVADO	VAPCO, INC. Evapeo			DWG.#	C4242412-DRA-ST	REV -
MODEL# ATC-2273E	NTS	LVAP	<i>-</i> 0, 1			SERIAL	#	DATE: 12/14/2025
NOTES 1. (M)- FAN MOTOR LOCATION 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDII GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DR. 4. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kf 5. *-APPROXIMATE DIMENSIONS DO NOT FOR PRE-FABRICATION OF CONNECT	NG AWINGS) Pa] T USE			FACE B		<u>F</u>	FACE C	FACE D
PIPING 6. 3/4" [19mm] DIA. MOUNTING HOLES. R RECOMMENDED STEEL SUPPORT DR 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]	EFER TO		7" [178]	PLAN VIEW 1'-3 1/4"	[387]		FACE A (4) ACCESS DOOR	
		5'-9 3/8" * 3'-0 3/8" *				CESS (M) ACCESS	ACCESS (M) ACCESS	\exists
4'-10 3/4" [1492]* (4) 4" [100] PE REFRIG IN REFRIG OU O 2'-1 1/4" [641]		[922] 4'-8 PE	1/8" [1426] -10" [2083] 19'-8 1/2 3/8" [2499]	"[6007]		or Door	DOOR DOOR	
1'-5" [432] 3 5/8" [92] (2) 3" [80] MPT (2) 2" [50] MPT MAKE-UP (2) 3" [80] MPT 5 1/8 DRAIN [130])] ''	11'-4 7/8" [1422] [3477] 11'-5 3/4" [3499] 11'-10" [3607]		2'-10 [87	3/8"3]		24'-1 3/4" [7360]	
24	-				F	FACE A		
SHIPPING 87820 lbs+ [39835] kg+	OPERA WEIG	ATING 114300 lbs+ [51850]	kg+	EAVIEST SECTION 3	37090 lbs+ [16825]	Luc	OF SHIPPING SECTIONS 4	DRAWN BY: JLG