

This document is the property of Evapco, Inc. It should not be copied or disclosed without prior written authorization.

MODEL #	U-SSTWE2-19R66H0100F1KA
---------	-------------------------


DWG. #	USSTW2-SE-6L
--------	--------------

DATE	7/17/2026
------	-----------



- 1) * = HANGER HOLE LOCATION.
- 2) HANGER HOLES ARE FOR 3/4 INCH THREADED ROD.
- 3) ALL DIMENSIONS ARE FOR REFERENCE AND SHOULD NOT BE USED FOR PREFABRICATION OF PIPING OR SUPPORTS.

A diagram of a two-fan unit, similar to the one in Figure 1. It features two circular fans with a black grille pattern. To the right of the fans is a large, empty rectangular box for labeling. The unit is shown from a top-down perspective with mounting brackets on the sides.



Technical drawing of a three-bay bridge structure. The drawing shows a side elevation with dimensions in feet and inches. The total length is 126 1/2'. The spans between the three piers are marked as * 42' each. The overhangs at the ends are 36 1/2' on the right and 5 3/4' on the left. The drawing includes details of the bridge deck, piers, and abutments.

- 2" MPT
DRAIN

ROOM

1300 lbs+ [590] kg+

1470 lbs+ [670] kg+