| CONDENSER | | | EV/AD/ | EVAPCO, INC. Evapea | | | DWG.# C4122410-DRA-ST REV - | | |
|---|---|--|--|---------------------|-------|------------------------|-----------------------------|----------------|----------|
| MODEL# | ATC-1026E | SCALE NT | EVAPO | JO, INC | | S | EERIAL# | DATE: | 2/8/2025 |
| 2. MPT DENOT FPT DENOT BFW DENO GVD DENOT FLG DENOT PE DENOTE ACCESSOR 4. MAKE-UP W 20 psi MIN [5. *-APPROXII FOR PRE-F, PIPING 6. 3/4" [19mm] RECOMMEN 7. DIMENSION | OTOR LOCATION TES MALE PIPE THR TES FEMALE PIPE TH DTES BEVELED FOR V ITES GROOVED TES FLANGE ES PLAIN END GHT DOES NOT INCL RIES (SEE ACCESSO) VATER PRESSURE [137 kPa], 50 psi MAX MATE DIMENSIONS DE TABRICATION OF CON IDIA. MOUNTING HOI NDED STEEL SUPPONS LISTED AS FOLLO NGLISH FT-IN | HREAD WELDING .UDE RY DRAWIN [344 kPa] DO NOT USE NNECTING LES. REFER | то | FACE B PLAN VIEW | | ACCESS DOOR | FACE C | DOCESS DOOR | FACE D |
| MI | ETRIC [mm] | | | | | | FACE A | | |
| | | _ | | 1'-3 1/4" [387 | 71– | _ | | | |
| | | | | () () () | | | | | |
| | | 9 3/8"* 762] | 4'-8 1/8"[1426] 3'-0 3/8" * [922] | | | (M) ACCESS DOOR | | ACCESS DOOR | |
| 4'-0 3/4"[1238]* | (2) 4" [100] PE | REFRIG OI | 6'-0"[1829] | | | | | | |
| 2" [50] MPT MAKE-UP 3" [80] MPT DRAIN 2'-1 1/4" [641] | | | 6" [152] * 6'-2 3/8" [1889] | (| | | | | |
| 3 5/8" [92] | 5 1/4" [133] 4 1/4" [108] 7'-2" [2184] | -10" | 1'-5" [432] — 3" [80] MPT OVERFLOW | 2'-10 3/8" [873] | | | 24'-1 3/4" [7360] | | |
| [3607] FACE A | | | | | | | | | |
| SHIPPING WEIGHT | 38540 lbs+ [17485] kg | g+ | DPERATING | kg+ HEAVIEST SEC | CTION | 31920 lbs+ [14480] kg+ | NO. OF SHIPPING SECTIONS 2 | DRAWN BY: | JLG |