CONDENSER			EV/AD/	EVAPCO, INC. Evaped			DWG.# C4122410-DRA-ST REV -		
MODEL #	ATC-1026E	SCALE NT	EVAPO	JO, TINC		S	ERIAL#	DATE:	2/8/2025
2. MPT DENOT FPT DENOT BFW DENOT GVD DENOT FLG DENOTE ACCESSOR 4. MAKE-UP W 20 psi MIN [15. *-APPROXIMFOR PRE-F/PIPING 6. 3/4" [19mm] RECOMMEN 7. DIMENSION	ES PLAIN END GHT DOES NOT INCL RIES (SEE ACCESSOI VATER PRESSURE 137 kPa], 50 psi MAX MATE DIMENSIONS D ABRICATION OF CON DIA. MOUNTING HOI NDED STEEL SUPPO IS LISTED AS FOLLO	HREAD WELDING UDE RY DRAWIN [344 kPa] DO NOT USE NNECTING LES. REFER	то	FACE B PLAN VIEW		ACCESS DOOR	FACE C	CESS DOOR	FACE D
ME	ETRIC [mm]						FACE A		
			7" [178]	1'-3 1/4" [387	71–	_	_		
		3/8"* 762]	4'-8 1/8"[1426] 3'-0 3/8" * [922]			(M) ACCESS DOOR		ACCESS	
4'-0 3/4"[1238]*	(2) 4* [100] PE	REFRIG 0	6'-0"[1829]]					
2" [50] MPT MAKE-UP 3" [80] MPT DRAIN 2'-1 1/4" [641]			6" [152] * 6'-2 3/8" [1889]	(
3 5/8" [92]	5 1/4" [133] 4 1/4" [108] 7'-2" [2184]	-10"	1'-5" [432] 3" [80] MPT OVERFLOW	2'-10 3/8" [873]			24'-1 3/4" [7360]		
[3607] FACE A									
SHIPPING WEIGHT	38540 lbs+ [17485] kg	g+	OPERATING WEIGHT 51580 lbs+ [23400]	kg+ HEAVIEST SEC	CTION	31920 lbs+ [14480] kg+	NO. OF SHIPPING SECTIONS 2	DRAWN BY:	JLG