

UNIT	CONDENSER	
MODEL #	PMRC-954	SCALE NTS

# EVAPCO, INC.




DWG. # CEWR12C2410-DRB-ST

REV -

**NOTES:**


1. (M)- FAN MOTOR LOCATION.
2. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED  
FLG DENOTES FLANGE  
PE DENOTES PLAIN END
3. +UNIT WEIGHT DOES NOT INCLUDE  
ACCESSORIES (SEE ACCESSORY DRAWINGS).
4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO  
RECOMMENDED STEEL SUPPORT DRAWING.
5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN,  
50 psi [344 kPa] MAX.
6. DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
[METRIC] [mm]
7. \* - APPROXIMATE DIMENSIONS DO NOT  
USE FOR PRE-FABRICATION OF CONNECTING PIPING

### FACE C



## FACE D

**FACE B**



## FACE B

## FACE A

**SHIPPING  
WEIGHT**

39160 lbs+ [17765] kg+

**OPERATING  
WEIGHT**

49790 lbs+ [22585] kg+

## HEAVIEST SECTION WEIGHT

28300 lbs+ [12840] kg+

**NO. OF SHIPPING SECTIONS**

2

DRAWN BY: **JLG**