
UNIT	CONDENSER		
MODEL #	PMRC-420	SCALE	NTS

EVAPCO, INC. EVAPCO


NOTES:


- 1. (M)- FAN MOTOR LOCATION.
- 2. MPT DENOTES MALE PIPE THREAD
 FPT DENOTES FEMALE PIPE THREAD
 BFW DENOTES BEVELED FOR WELDING
 GVD DENOTES GROOVED
 FLG DENOTES FLANGE
 PE DENOTES PLAIN END
- 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS).
- 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX.
- 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]
- 7. *- APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.

FACE C



FACE A





FACE A

NO. OF SHIPPING SECTIONS

DRAWN BY: JL

SHIPPING WEIGHT 15680 lbs+ [7115] kg+

OPERATING WEIGHT 20370 lbs+ [9240] kg+

HEAVIEST SECTION WEIGHT

9970 lbs+ [4525] kg+

OF CHILLING CECTIONS

JLG