CONDENSER CEWR121214-DRA-ST EVAPCO, INC. Evapco SERIAL# MODEL# SCALE NTS PMRC-600 11/27/2025 NOTES: 1. (M)- FAN MOTOR LOCATION. 2. MPT DENOTES MALE PIPE THREAD **FACE C** FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS). 4, 3/4" [19mm] DIA, MOUNTING HOLES, REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, **FACE B FACE D** 50 psi [344 kPa] MAX. 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN **PLAN VIEW** [METRIC] [mm] 7. \* - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING. **FACE A** 3'-0 7/8" 5'-8 5/8" 3 [937] [1743] (2) 4" [100] PE REFRIG IN 3'-11 3/4" [1213] \* 7'-2 5/8" [2200] 0 0 -REFRIG OUT (2) 4" [100] PE OVERSIZED 15'-9" [4801] **ACCESS DOORS** 5 1/8" [130]-2"[50] MPT 9'-11" [3023] \* MAKE UP 8'-6 3/8" [2600] 3"[80] MPT DRAIN 2'-5"[737] 1'-8" [508] 3 7/8" [98] 3"[80] MPT 11'-11 3/4" -4 3/4" [121] 1'-7 1/8" [486]-OVERFLOW [3651] 5'-0 3/8" [1534] 11'-10 3/8" [3616]

HEAVIEST SECTION

WEIGHT

19620 lbs+ [8900] kg+

FACE A

NO. OF SHIPPING SECTIONS

DRAWN BY:

**JLG** 

**FACE B** 

25630 lbs+ [11630] kg+

OPERATING

WEIGHT

30710 lbs+ [13930] kg+

SHIPPING

WEIGHT