

UNIT	CONDENSER	
MODEL #	PMRC-690	SCALE NTS

EVAPCO, INC.




DWG. # CEWRTM1808-DRA-ST

REV -

NOTES:

1. (M)- FAN MOTOR LOCATION.
2. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
3. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS).
4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN,
50 psi [344 kPa] MAX.
6. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
7. * - APPROXIMATE DIMENSIONS DO NOT
USE FOR PRE-FABRICATION OF CONNECTING PIPING



FACE B

**SHIPPING
WEIGHT**

23480 lbs+ [10655] kg+

OPERATING WEIGHT

29350 lbs+ [13315] kg+

HEAVIEST SECTION WEIGHT


15510 lbs+ [7040] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY: **JLG**


FACE C



FACE B

PLAN VIEW

FACE D



FACE A