

UNIT	CONDENSER
MODEL #	PMRC-1988

EVAPCO, INC.




DWG. # CEWR123612-DRA-ST

REV -
SERIAL #
DATE: 1/15/2026

NOTES:

- (M)- FAN MOTOR LOCATION.
- MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS).
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
- MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN,
50 psi [344 kPa] MAX.
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
- * - APPROXIMATE DIMENSIONS DO NOT
USE FOR PRE-FABRICATION OF CONNECTING PIPING.


FACE C



FACE B

PLAN VIEW

FACE A



FACE B

FACE A

SHIPPING
WEIGHT

67220 lbs+ [30495] kg+

OPERATING
WEIGHT

82410 lbs+ [37385] kg+

HEAVIEST SECTION
WEIGHT

25140 lbs+ [11405] kg+

NO. OF SHIPPING SECTIONS

3

DRAWN BY: JLG