CONDENSER CONDENSER		[NC evapco	CEWR123610-DRA-ST	REV -
ODEL# PMRC-1712 SCALE NT	EVAPCO, I	INC. evapco	SERIAL#	DATE: 11/27/2025
NOTES: 1. (M)- FAN MOTOR LOCATION. 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS). 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX. 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 7. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.	FACE B PLAN VIEW	FACE C		FACE D
		FACE A		
3'-0 7/8" * <u>5'</u> -8 5/8" * [937] [1743]				
OVERSIZED — O — REFRIG IN OVERSIZED — O — REFRIG IN OUT	3'-3 1/4" [997] * 6'-6 1/8" [1984]			
3"[80] MPT 5 1/8" MAKE UP [130] 3"[80] MPT DRAIN 2'-5"[737]	9'-11" [3023] * 8'-6 3/8" [2600]			
1'-8" [508] 4 3/4" [121] (2) 3"[80] M OVERFLOW [1534] 41 10 3/9"	1'-8" - - -	36'-2"_ [11024]		1'-6 1/4" [464]
11'-10 3/8" [3616]	 	-		
FACE B	OPERATING 74070 " FOOOTO"	FACE A	NO OF CHIPPING SECTIONS	DRAWN BY: JLG
SHIPPING 59770 lbs+ [27115] kg+	OPERATING WEIGHT 74670 lbs+ [33870] kg+	HEAVIEST SECTION 21790 lbs+ [9885] kg+	NO. OF SHIPPING SECTIONS 3	l Jrg