							Dung #	Lasy	,
JNIT	CONDENSER		_ EV∧D€	'O TN	evapco		DWG.# CEWRTM3612-DRA-ST	REV	-
MODEL #	PMRC-1438	SCALE NTS	EVAPO	O, III			SERIAL #	DATE: 11/2	27/2025
2. MPT DENC FPT DENC BFW DENI GVD DENC FLG DENC FLG DENC FLG DENC ACCESSO 4. 3/4" [19mm RECOMMI 5. MAKE-UP 50 psi [344 6. DIMENSIC ENGLISH [METRIC] 7. * - APPRO		VINGS). FER TO WING. ' kPa] MIN,	<u>FACE B</u> <u>PLAN VIEW</u>			FACE C			FACE D
		4'-9" * 14401——				FACE A			
A(E 2"[50] MI MAKE (3"[80]	RSIZED (4) 4" [100] PE CCESS DOORS IPT UP	REFRIG OUT	3'-11 3/4" [1213] * 7'-2 5/8" [22 15'-9" [4801] 9'-11" [3023] * 8'-6 3/8" [26						
2'-5"[737] 1'-8" [508 3 7/8" [[130] 3'-10 1/2" [1181] 9'-	-9 3/4" 2991]	3"[80] MPT [508] OVERFLOW			36'-2" [11024]	(M) (M)		1'-6 1/4" [464]
		CE B				FACE A	1		
SHIPPING WEIGHT	56840 lbs+ [25785]	kg+	DPERATING 69360 lbs+ [31465] ki	rg+ HEAVIEST S	21260 lbs+ [96	45] kg+	NO. OF SHIPPING SECTIONS	DRAWN BY:	LG