JNIT	CONDENSER			VADCO '		vapco	DWG.# CEWRTM3610-DRA-ST	REV -
MODEL #	PMRC-1148	SCALE NTS	<i>;</i>	VAPCO, 1	TIAC'		SERIAL#	DATE: 11/25/2025
BFW DENOTES BI GVD DENOTES GI FLG DENOTES FL PE DENOTES FL ACCESSORIES (SI 4. 3/4" [19mm] DIA RECOMMENDED 5. MAKE-UP WATER 50 psi [344 kPa] I 6. DIMENSIONS LIS ENGLISH FT-IN [METRIC] [mm] 7. * - APPROXIMATE	ALE PIPE THREAD MALE PIPE THREAD EVELED FOR WELDING ROOVED ANGE IN END DOES NOT INCLUDE EE ACCESSORY DRAWINGS) MOUNTING HOLES. REFER STEEL SUPPORT DRAWING PRESSURE 20 psi [137 kPa] MAX. TED AS FOLLOWS:	R TO] MIN,		FACE B PLAN VIEW		FACE C		FACE D
		-9" * 448]				FACE A		
OVERSIZED :	(4) 4" [100] PE	REFRIG IN REFRIG OUT	3'-3 1/4" [997] *	6'-6 1/8" [1984]		46/4		
ACCESS DOORS 2"[50] MPT MAKE UP 3"[80] MPT DRAIN			15'-0 1/2" [45 9'-11" [3023] *	8'-6 3/8" [2600]				
3 7/8" [98] ^{_]} 3'-	4 3/4" [121] 5 1/8" [130] 10 1/2" 1181] 9'-9	9 3/4"	3"[80] MPT OVERFLOW	1'-8"		36'-2" [11024]		1'-6 1/4" [464]
	FAC	2991] CE B				FACE A	!	
SHIPPING WEIGHT	50230 lbs+ [22785] kg	kg+ OF	PERATING 6252 WEIGHT	520 lbs+ [28360] kg+	HEAVIEST SECTION WEIGHT	18210 lbs+ [8260] kg+	NO. OF SHIPPING SECTIONS	DRAWN BY: JLG