

CONDENSER CEWRTM1212-DRA-ST EVAPCO, INC. Evapco SERIAL# MODEL# SCALE NTS PMRC-411 NOTES: 1. (M)- FAN MOTOR LOCATION. 2. MPT DENOTES MALE PIPE THREAD


- FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END
- 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS).
- 4, 3/4" [19mm] DIA, MOUNTING HOLES, REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX.
- 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]
- 7. \* APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.

## **FACE C**



## **FACE A**





**FACE A** 

NO. OF SHIPPING SECTIONS

DRAWN BY: **JLG** 

19530 lbs+ [8860] kg+

WEIGHT

OPERATING WEIGHT

23470 lbs+ [10650] kg+

HEAVIEST SECTION WEIGHT

14370 lbs+ [6520] kg+

11/27/2025