

UNIT	CONDENSER
MODEL #	PMRC-369

EVAPCO, INC.



DWG. # CEWRTM1206-DRA-ST

REV -


SERIAL #

DATE: 1/15/2026

NOTES:

- (M) - FAN MOTOR LOCATION.
- MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS).
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
- MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN,
50 psi [344 kPa] MAX.
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
- * - APPROXIMATE DIMENSIONS DO NOT
USE FOR PRE-FABRICATION OF CONNECTING PIPING.


FACE C



FACE B


PLAN VIEW

FACE D



FACE B

FACE A



FACE A

SHIPPING
WEIGHT

13880 lbs+ [6300] kg+

OPERATING
WEIGHT

17590 lbs+ [7980] kg+

HEAVIEST SECTION
WEIGHT

8590 lbs+ [3900] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY: JLG