

UNIT	CONDENSER
MODEL #	PMRC-558

SCALE	NTS
-------	-----

EVAPCO, INC.



DWG. # CEWRTM1806-DRA-ST

REV -


SERIAL #

DATE: 1/15/2026

NOTES:


1. (M)- FAN MOTOR LOCATION.
2. MPT DENOTES MALE PIPE THREAD
3. FPT DENOTES FEMALE PIPE THREAD
4. BFW DENOTES BEVELED FOR WELDING
5. GVD DENOTES GROOVED
6. FLG DENOTES FLANGE
7. PE DENOTES PLAIN END
3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS).
4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX.
6. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
7. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.

FACE C




FACE D

FACE B
PLAN VIEW



FACE B



FACE A

SHIPPING
WEIGHT

20100 lbs+ [9120] kg+

OPERATING
WEIGHT

25850 lbs+ [11730] kg+

HEAVIEST SECTION
WEIGHT

12580 lbs+ [5710] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY: JLG