

UNIT	CONDENSER
MODEL #	PMRC-949

EVAPCO, INC.



DWG. # CEWR122010-DRA-ST


REV -

SERIAL #

DATE: 1/14/2026

NOTES:


- (M) - FAN MOTOR LOCATION.
- MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
- UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS).
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX.
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
- * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.



FACE B


PLAN VIEW

FACE C



FACE D

FACE A



FACE A

SHIPPING
WEIGHT

33690 lbs+ [15285] kg+

OPERATING
WEIGHT

41760 lbs+ [18945] kg+

HEAVIEST SECTION
WEIGHT

24120 lbs+ [10945] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY: JLG