

UNIT	CONDENSER	
MODEL #	PMRC-715	SCALE NTS


EVAPCO, INC.



DWG. #	CEWR122012-DRA-ST	REV	-
SERIAL #		DATE:	1/15/2026


NOTES:

1. (M)- FAN MOTOR LOCATION.
2. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
3. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS).
4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN,
50 psi [344 kPa] MAX.
6. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
7. * - APPROXIMATE DIMENSIONS DO NOT
USE FOR PRE-FABRICATION OF CONNECTING PIPE



FACE B


PLACE C



FACE B

PLAN VIEW

FACE D



FACE A

SHIPPING WEIGHT 36880 lbs+ [16730] kg+ OPERATING WEIGHT 45120 lbs+ [20470] kg+ HEAVIEST SECTION WEIGHT 28190 lbs+ [12790] kg+ NO. OF SHIPPING SECTIONS 2 DRAWN BY: JLG