

| | |
|---------|---------------|
| UNIT | CONDENSER |
| MODEL # | eco-PMRC-1148 |

EVAPCO, INC.




DWG. # CEWR124004-DRA-ST

REV -
SERIAL #
DATE: 2/19/2026

NOTES:


1. (M)- FAN MOTOR LOCATION.
2. MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS).
4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX.
6. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
7. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.

FACE C



FACE B
PLAN VIEW

FACE A



SHIPPING
WEIGHT

46470 lbs+ [21080] kg+

OPERATING
WEIGHT

61910 lbs+ [28085] kg+

HEAVIEST SECTION
WEIGHT

16050 lbs+ [7285] kg+

NO. OF SHIPPING SECTIONS

3

DRAWN BY: JLG