

This document is the property of Evapco, Inc. It should not be copied or disclosed without prior written authorization.

MODEL #

SCALE


DWG. #

REV.	0
------	---

Technical drawing of the rear view of the vehicle. It shows the rear door, rear window, and rear wheel. A large, faint watermark reading 'Preview' is overlaid diagonally across the center of the image.

- NEMA 4X
JUNCTION BOX

- 1) * = HANGER HOLE LOCATION.
- 2) RIGHT HAND MODEL SHOWN.
- 3) HANGER HOLES ARE FOR 3/4 INCH THREADED ROD.
- 4) WATER DEFROST ADDS 1 3/4" INCHES TO HEIGHT OF STANDARD UNIT AND CHANGES DRAIN SIZE.
- 5) ALL DIMENSIONS ARE FOR REFERENCE AND SHOULD NOT BE USED FOR PREFABRICATION OF PIPING OR SUPPORTS.
- 6) **= HEIGHT OF SUCTION HEADER AND INSTALLED THERMOWELL FITTING ABOVE CABINET. CUSTOMER IS RESPONSIBLE TO ACCOUNT FOR ADDITIONAL HEIGHT NECESSARY FOR RTD AND ACCESS.



Technical drawing of a 2-inch MPT drain assembly. The drawing shows a side view of the assembly with various dimensions and labels.

Labels:

- N BOX
- AIR FLOW
- 2" MPT DRAIN

Dimensions:

- Top horizontal dimension: $45 \frac{3}{8}$
- Left vertical dimension: $3 \frac{3}{4}$
- Top horizontal dimension (from left edge to center): $* 41 \frac{3}{8}$
- Top horizontal dimension (from center to right edge): $3 \frac{3}{4}$
- Right vertical dimension (from top to center): $4 \frac{7}{8}$
- Right vertical dimension (from center to bottom): $9 \frac{1}{4}$ (labeled with **)
- Right vertical dimension (from bottom to top): $49 \frac{1}{2}$
- Right vertical dimension (from bottom to top): $54 \frac{3}{4}$
- Bottom horizontal dimension (from left edge to center): $1 \frac{1}{4}$
- Bottom horizontal dimension (from center to right edge): $1 \frac{1}{4}$
- Bottom horizontal dimension (from left edge to right edge): 55
- Bottom horizontal dimension (from left edge to right edge): $57 \frac{1}{2}$

ROOM

SHIPPING
WEIGHT

OPERATING WEIGHT	10000
------------------	-------

1430 lbs+ [650] kg+