


UNIT	eco-LRWB 5-6L12-Z
TITLE	EXTERNAL SERVICE PLATFORM

EVAPCO, INC.



DWG. #	PLWZ0918-DA		
SCALE	N.T.S.	DRAWN BY	SLR

MODEL #	H DIM	
	FT-IN	[mm]
ESWA 153-23H, 23I, 23J	8'-10 1/2 "	2705
ESWA 153-24H, 24I, 24J	9'-6"	2896
ESWA 153-25H, 25I, 25J	10'-1 1/2 "	3086
ESWA 153-26H, 26I, 26J	10'-9"	3277
ESWA 153-33H, 33I, 33J	9'-10 1/2 "	3010
ESWA 153-34H, 34I, 34J	10'-6"	3200
ESWA 153-35H, 35I, 35J	11'-1 1/2 "	3391
ESWA 153-36H, 36I, 36J	11'-9"	3581
ESWA 153-43I, 43J, 43K	10'-10 1/2 "	3315
ESWA 153-44I, 44J, 44K	11'-6"	3505
ESWA 153-45I, 45J, 45K	12'-1 1/2 "	3696
ESWA 153-46I, 46J, 46K	12'-9"	3886



NOTES:

1. LADDER AND PLATFORM SHIP LOOSE. FIELD INSTALLATION BY OTHERS IS REQUIRED.
2. THE BOTTOM OF THE LADDER DOES NOT EXTEND PAST THE BASE OF THE UNIT.
IF THE UNIT IS ELEVATED THEN AN OPTIONAL EXTENDED LADDER PACKAGE SHOULD BE CONSIDERED. (CONSULT FACTORY)
3. REFER TO RIGGING PACK FOR LADDER AND PLATFORM MOUNTING INSTRUCTIONS.
4. EACH PLATFORM AND LADDER ASSY. WEIGHS 1100 LBS. [499 KG]
5. MODELS ESWA 153-23H, 23I, 23J DO NOT REQUIRE AN INTERMEDIATE LADDER BRACKET.
6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN
[METRIC] mm