UNIT	COOLING TOWER	
MODEL #	AT 312-3I42	SCALE NTS


EVAPCO, INC. Evapeo

DWG. # T3124236-DRD-ST REV. 
SERIAL # DATE 11/14/2025

## NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD
  FPT DENOTES FEMALE PIPE THREAD
  BFW DENOTES BEVELED FOR WELDING
  GVD DENOTES GROOVED
  FLG DENOTES FLANGE
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
- 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm]


## FACE C



**FACE B** 


**PLAN VIEW** 






**FACE D** 

## **FACE A**





SHIPPING WEIGHT 27540 lbs+ [12495] kg+ OPERATING WEIGHT

49530 lbs+ [22470] kg+

HEAVIEST SECTION WEIGHT

6020 lbs+ [2735] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: KDS