



| | | | | |
|------------------------------|--------------|--------------------------------------------------------------------------------------------------------|---------------------------|------------------|
| UNIT COOLING TOWER | | EVAPCO, INC.  | DWG. # T3091136-DRD-ST | REV. - |
| MODEL # AT 19-3K11 | SCALE NTS | | SERIAL # | DATE 7/8/2025 |

NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMENDED STEEL SUPPORT DRAWING.
7. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]


FACE C




FACE D

FACE B

PLAN VIEW



FACE B



FACE A

| | | | | | | | | |
|-----------------|----------------------|------------------|----------------------|-------------------------|----------------------|--------------------------|---|---------------|
| SHIPPING WEIGHT | 5170 lbs+ [2350] kg+ | OPERATING WEIGHT | 8470 lbs+ [3845] kg+ | HEAVIEST SECTION WEIGHT | 3570 lbs+ [1620] kg+ | NO. OF SHIPPING SECTIONS | 2 | DRAWN BY: JLG |
|-----------------|----------------------|------------------|----------------------|-------------------------|----------------------|--------------------------|---|---------------|