UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS ATWB 24-7M28

EVAPCO, INC. Evapeo





DWG. # REV. WB3242814-DRC-ST DATE 11/5/2025 SERIAL #


## NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]

## **FACE C**







DRAWN BY: SLR NO. OF SHIPPING SECTIONS **SHIPPING OPERATING** HEAVIEST SECTION 24480 lbs+ [11105] kg+ 110360 lbs+ [50060] kg+ 166180 lbs+ [75380] kg+ WEIGHT WEIGHT WEIGHT