

UNIT	CONDENSER
MODEL #	eco-PMRC-1626

EVAPCO, INC. 

DWG. # CEWR123608-DRA-ST

REV -


SERIAL #

DATE: 2/20/2026


NOTES:

- (M)- FAN MOTOR LOCATION.
- MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS).
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
- MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN,
50 psi [344 kPa] MAX.
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
- * - APPROXIMATE DIMENSIONS DO NOT
USE FOR PRE-FABRICATION OF CONNECTING PIPING.

FACE C



FACE A



FACE B

SHIPPING
WEIGHT

63120 lbs+ [28635] kg+

OPERATING
WEIGHT

77740 lbs+ [35265] kg+

HEAVIEST SECTION
WEIGHT

23850 lbs+ [10820] kg+

NO. OF SHIPPING SECTIONS

3

DRAWN BY: JLG

FACE A