UNIT	CLOSED CIRCUIT COOLER	
MODEL #	ATWB 12-7N14-Z	SCALE NTS
NOTES:		



DWG. # REV. WB3121414-DRC-SF DATE 11/4/2025 SERIAL #

- 1. (M) FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. + UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE SEPARATE DRAWINGS FOR ACCESSORIES)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. * APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER **DRAIN BY OTHERS**
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.

27700 lbs+ [12565] kg+

WEIGHT

9. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN [METRIC] MM


SHIPPING

WEIGHT



FACE C

FACE B PLAN VIEW




FACE D

DRAWN BY: JLG

FACE A

24640 lbs+ [11180] kg+

WEIGHT



41620 lbs+ [18880] kg+