

UNIT	CONDENSER
MODEL #	eco-PMRC-1904

EVAPCO, INC. 

DWG. # CEWR123612-DRA-ST

REV -


SERIAL #

DATE: 2/20/2026

NOTES:

- (M)- FAN MOTOR LOCATION.
- MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
- UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS).
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX.
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
- * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.


FACE C



FACE B

PLAN VIEW

FACE A



SHIPPING
WEIGHT

83130 lbs+ [37710] kg+

OPERATING
WEIGHT

98320 lbs+ [44600] kg+

HEAVIEST SECTION
WEIGHT

33470 lbs+ [15185] kg+

NO. OF SHIPPING SECTIONS

3

DRAWN BY: **JLG**