

UNIT	CONDENSER
MODEL #	eco-PMRC-1849

**EVAPCO, INC.**




DWG. # CEWR123610-DRA-ST

REV -  
SERIAL #  
DATE: 2/20/2026

**NOTES:**

- (M)- FAN MOTOR LOCATION.
- MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
- UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS).
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX.
- DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
[METRIC] [mm]
- \* - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.


**FACE C**




**FACE B**

**PLAN VIEW**

**FACE A**



**FACE B**



**FACE A**

SHIPPING  
WEIGHT

73770 lbs+ [33465] kg+

OPERATING  
WEIGHT

88670 lbs+ [40225] kg+

HEAVIEST SECTION  
WEIGHT

28790 lbs+ [13060] kg+

NO. OF SHIPPING SECTIONS

3

DRAWN BY: **JLG**