UNIT **CLOSED CIRCUIT COOLER** MODEL # ATWB 24-6L14-Z NTS

EVAPCO, INC. evapco



DWG. # REV. WB3241412-DRC-SF DATE 11/5/2025 SERIAL #

## NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. \*-APPROXIMATE DIMENSIONS DO NOT USE
- FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]




**FACE C** 


FACE D

(2) ACCESS DOOR

## **FACE B PLAN VIEW**



## **FACE A**



**SHIPPING** WEIGHT

48780 lbs+ [22130] kg+

OPERATING WEIGHT

74720 lbs+ [33895] kg+

HEAVIEST SECTION WEIGHT

21330 lbs+ [9680] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: JLG