UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS eco-ATWB 4-3G12

## EVAPCO, INC. Evapco




DWG. # REV. WB3041206-DRE-ST DATE 11/19/2025 SERIAL #


## NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]

**FACE B PLAN VIEW** 



**FACE A** 





DRAWN BY: **SHIPPING** OPERATING HEAVIEST SECTION NO. OF SHIPPING SECTIONS 5840 lbs+ [2650] kg+ 8740 lbs+ [3965] kg+ 5020 lbs+ [2280] kg+ WEIGHT WEIGHT WEIGHT