

This document is the property of Evapco, Inc. It should not be copied or disclosed without prior written authorization.

MODEL #	U-EJETME2-1943H0050F1JA
---------	-------------------------

DWG. # UEJETM2-SE-16,18

DATE	9/14/2025
------	-----------



Technical drawing of the front view of a device. The drawing shows two circular fans with a grid pattern, mounted on a rectangular frame. The dimensions are as follows:

- Overall width:  $126 \frac{3}{8}$
- Distance from left edge to first fan center:  $6$
- Distance between fan centers:  $42$  (indicated by two arrows, each labeled  $* 42$ )
- Distance from second fan center to right edge:  $36 \frac{3}{8}$
- Distance from left edge to first fan center (bottom):  $4$
- Distance between fan centers (bottom):  $42$  (indicated by two arrows, each labeled  $42$ )
- Distance from second fan center to right edge (bottom):  $38 \frac{5}{8}$

2" MPT  
DRAIN

- 1) \* = HANGER HOLE LOCATION.
- 2) RIGHT HAND MODEL SHOWN.
- 3) HANGER HOLES ARE FOR 3/4 INCH THREADED ROD.
- 4) WATER DEFROST ADDS 1 3/4" INCHES TO HEIGHT OF STANDARD UNIT AND CHANGES DRAIN SIZE.
- 5) ALL DIMENSIONS ARE FOR REFERENCE AND SHOULD NOT BE USED FOR PREFABRICATION OF PIPING OR SUPPORTS.
- 6) \*\*= HEIGHT OF SUCTION HEADER AND INSTALLED THERMOWELL FITTING ABOVE CABINET. CUSTOMER IS RESPONSIBLE TO ACCOUNT FOR ADDITIONAL HEIGHT NECESSARY FOR RTD AND ACCESS.



ROOM

990 lbs+ [450] kg+

1060 lbs+ [485] kg+